



**THE DATASHEET OF
SI4708-B-GMR**



User Registration

Register today to create your account on Silabs.com. Your personalized profile allows you to receive technical document updates, new product announcements, "how-to" and design documents, product change notices (PCN) and other valuable content available only to registered users. <http://www.silabs.com/profile>

| PCN Date: 16Mar10 | | Effective Date: 16June10 | | | | | | | | | | | | | | | |
|---|--|---|--------------------------------|----------------------|--------------|---------------|-------------|--------------|-------------|---------------|-------------|--------------|-------------|--------------|-------------|--------------|-------------|
| Title: Si4708/Si4709 Min Order Quantity (MOQ) Reel Change from 2.5K to 5K/Datasheet rev 1.4 | | | | | | | | | | | | | | | | | |
| Originator: Kenneth Kong | Phone: 65 6511778 | Dept: Supplier Management | | | | | | | | | | | | | | | |
| Customer Contact: kathy Hagger | Phone: 512-532-55261 | Dept: Sales/Customer Service | | | | | | | | | | | | | | | |
| PCN Type: | | | | | | | | | | | | | | | | | |
| <input type="checkbox"/> Assembly | <input type="checkbox"/> Discontinuance | <input type="checkbox"/> Package | <input type="checkbox"/> Test | | | | | | | | | | | | | | |
| <input type="checkbox"/> Datasheet | <input type="checkbox"/> Fabrication | <input type="checkbox"/> Product Revision | | | | | | | | | | | | | | | |
| <input checked="" type="checkbox"/> Packing | <input checked="" type="checkbox"/> Labeling | <input type="checkbox"/> Location | <input type="checkbox"/> Other | | | | | | | | | | | | | | |
| Last Order Date: 16June10 | | | | | | | | | | | | | | | | | |
| PCN Details | | | | | | | | | | | | | | | | | |
| Description of Change: | | | | | | | | | | | | | | | | | |
| Change the Minimum Order Quantity (MOQ) reel size from a 2.5K reel to a 5K reel for Si4708 & Si4709 ordering part numbers. | | | | | | | | | | | | | | | | | |
| There is no change to the Reel type, Carrier tape or Cover tape. | | | | | | | | | | | | | | | | | |
| In addition, the Si4708/09 datasheet has been revised to version 1.4 to detail the revised MOQ reel size change. | | | | | | | | | | | | | | | | | |
| Reason for Change: | | | | | | | | | | | | | | | | | |
| Improve test supplier efficiency by changing to a larger quantity reel for MOQ product shipments for Si4708 & Si4709. | | | | | | | | | | | | | | | | | |
| Impact on Form, Fit, Function, Quality, Reliability: | | | | | | | | | | | | | | | | | |
| There is no impact on form, fit, function, quality or reliability. | | | | | | | | | | | | | | | | | |
| Product Identification: | | | | | | | | | | | | | | | | | |
| Products ordered under the following ordering part numbers are affected by this change: | | | | | | | | | | | | | | | | | |
| <table border="1" style="margin-left: auto; margin-right: auto;"> <thead> <tr> <th>Ordering Part Number</th> <th>Package size</th> </tr> </thead> <tbody> <tr> <td>Si4708-B-ZM6R</td> <td>2.5x2.5 QFN</td> </tr> <tr> <td>Si4708-B-GMR</td> <td>2.5x2.5 QFN</td> </tr> <tr> <td>Si4709-B-ZM6R</td> <td>2.5x2.5 QFN</td> </tr> <tr> <td>Si4709-B-GMR</td> <td>2.5x2.5 QFN</td> </tr> <tr> <td>Si4708-C-GMR</td> <td>2.5x2.5 QFN</td> </tr> <tr> <td>Si4709-C-GMR</td> <td>2.5x2.5 QFN</td> </tr> </tbody> </table> | | | | Ordering Part Number | Package size | Si4708-B-ZM6R | 2.5x2.5 QFN | Si4708-B-GMR | 2.5x2.5 QFN | Si4709-B-ZM6R | 2.5x2.5 QFN | Si4709-B-GMR | 2.5x2.5 QFN | Si4708-C-GMR | 2.5x2.5 QFN | Si4709-C-GMR | 2.5x2.5 QFN |
| Ordering Part Number | Package size | | | | | | | | | | | | | | | | |
| Si4708-B-ZM6R | 2.5x2.5 QFN | | | | | | | | | | | | | | | | |
| Si4708-B-GMR | 2.5x2.5 QFN | | | | | | | | | | | | | | | | |
| Si4709-B-ZM6R | 2.5x2.5 QFN | | | | | | | | | | | | | | | | |
| Si4709-B-GMR | 2.5x2.5 QFN | | | | | | | | | | | | | | | | |
| Si4708-C-GMR | 2.5x2.5 QFN | | | | | | | | | | | | | | | | |
| Si4709-C-GMR | 2.5x2.5 QFN | | | | | | | | | | | | | | | | |
| Last Date of Unchanged Product: 16June10 | | | | | | | | | | | | | | | | | |
| Following the Effective Date of this PCN, Silicon Laboratories will ship MOQ's for the above identified products on 5K Reels only. | | | | | | | | | | | | | | | | | |

Looking for pricing, stock, or lifecycle information?

Click below to explore more details on WIN SOURCE:

 [View SI4708-B-GMR on WIN SOURCE](#)

 [Silicon Labs](#) Information

Optimize Your Supply Chain with WIN SOURCE Solutions

-  Global Sourcing Solution
-  Obsolete Management
-  Cost Control Management
-  Shortage Management
-  Alternative Solution
-  Excess Inventory Management